

## SVHB clamp holder, positive

For copy and longitudinal face turning using VB indexable inserts

**ATORN**<sup>®</sup>

### Application

For copy, longitudinal and face turning with VB indexable insert, 35°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVHBR 1212 F11

### Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



<b>Art. no.</b>	<b>17836 302</b>
<b>ISO name</b>	SVHB R/L 1616 H11
<b>Shaft height</b>	16 mm
<b>Shank width</b>	16 mm
<b>Length</b>	100 mm
<b>Length of head</b>	13.4 mm
<b>Programming size</b>	20 mm
<b>Suitable for indexable inserts</b>	VB.. 1103..
<b>Tool design</b>	Right

### EAN-Code

4050293563375