

## Sliding door cabinet with doors with viewing window, height 1200 mm

With shelves, load capacity 80 kg per shelf

### Execution:

- Stable welded sheet steel structure with base, available in three different heights, widths and depths
- Galvanised shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Sliding doors with reinforcement pockets and recessed handle, guide rail with special rollers and anti-crush protection, cushioned end stops
- Doors can be locked simultaneously with a push and turn cylinder lock, incl. 2 keys

### Delivery:

Available on request: DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other paint finishes.

<b>Art. no.</b>	<b>50146 235</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50146235
<b>Door design</b>	Inspection glass
<b>Height</b>	1200 mm
<b>Depth</b>	500 mm
<b>Width</b>	1000 mm
<b>With partition wall</b>	No
<b>Number of folder height</b>	3 PCS
<b>Number of shelves</b>	2 PCS
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Load-carrying capacity</b>	400 kg
<b>Lock type</b>	Cylinder lock
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	44.000 kg
<b>Product Group</b>	504

### EAN

4053625449842