

Platform trolley, nestable, with fixed basket

Type: Shopping trolley



Execution:

- Ergonomic handle.
- 1 lower load area and 1 basket
- Height up to the lower load area: 200 mm
- Load capacity per load area: 100 kg
- Height to handle: 1,200 mm
- Castors: 4 swivel castors
- Castor diameter: 125 mm

Advantage:

- Nestable = can be pushed together = saves space



Art. no.	50200 016
Brand	KONGAMEK
Manufacturer Part Number	KM4202-KD-E
Load-carrying capacity of loading surfaces	100 kg
Load-carrying capacity	200 kg
Length	980 mm
Width	530 mm
Height	1210 mm
Colour	Silver coloured
Number of steering rollers	4 PCS
With wheel lock	No
Wheel diameter	125 mm
Material of wheel	TPE
Made in	Vietnam
Number of loading surfaces	2 PCS
Gross Weight	24.500 kg
Product Group	5AT

EAN

7350074809188