

## Pneumatic ratchet screwdriver MR-2207C

For assembly and disassembly in hard-to-reach places



<b>Art. no.</b>	<b>75066 280</b>
<b>Brand</b>	TOKU
<b>Manufacturer Part Number</b>	MR-2207C
<b>Model</b>	MR-2207C
<b>Suitable for screw</b>	M8
<b>Max. tightening torque</b>	28 Nm
<b>Max. idle speed</b>	250 rpm
<b>Air consumption</b>	5 l/s
<b>Tool holding device</b>	1/4-inch external square
<b>Length</b>	165 mm
<b>Connection thread</b>	1/4 inch
<b>Inner hose diameter</b>	6.5 mm
<b>Sound-pressure level</b>	81 dB
<b>Weight</b>	0.5 kg
<b>Gross Weight</b>	0.604 kg
<b>Product Group</b>	7AE



### EAN

8717981052943