



### BN 22314

#### Cable glands

with metric thread

Brass

nickel plated

- Dome nut: brass CuZn39Pb3, nickel-plated
- Sealing insert: fluorine rubber FKM
- Gland body: brass CuZn39Pb3, nickel-plated
- O-Ring: fluorine rubber FKM
- Connecting thread: metric, as per EN 60423
- Sealing insert and O-ring have a very good resistance to many chemicals
- Especially suitable for high temperature applications
- Large-area sealing protects the cable
- Integrated anchorage with high retention
- Wide sealing and clamping range
- The inner sealing ring can be removed easily for larger cables
- High UV, ozone and weather resistance
- Temperature range: -40 °C / +200 °C (dynamic)
- Protection grade: IP66 / IP67 / IP69



Test standard: EN 62444  
EMC-version available on request



Article#	d <sub>1</sub>	Clamping range	C <sub>2</sub> Clamping range	C <sub>1</sub> Clamping range	SW1	SW2	L	L <sub>1</sub>	Code
9003840	M12x1,5	3-8	3-5	5-8	16	16	6,5	25,5	K155-1012-00
9003842	M16x1,5	5-10,5	5-7,5	7,5-10,5	20	20	7	31,5	K155-1016-00
9003843	M20x1,5	8-15	8-10,5	10,5-15	25	25	8	33	K155-1020-00
9003844	M25x1,5	14-20,5	14-15,5	15,5-20,5	32	32	8	35,5	K155-1025-00
9003845	M32x1,5	18-25,5	18-20,5	20,5-25,5	36	36	9	40,5	K155-1032-00
9003846	M40x1,5	24-33	24-29	29-33	45	45	9	43	K155-1040-00
9003847	M50x1,5	32-42	32-37,5	37,5-42	55	55	10	47,5	K155-1050-00
9003848	M63x1,5	40-53	40-46	46-53	70	70	10	53	K155-1063-00