

GN 653.2 | Retained screws with knurled grip knob

Steel or stainless steel





- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- RH

STANDARD EXECUTIONS

- **GN 653.2-ST**: turned and black-oxide steel, class 5 (tensile strength 500 N/mm²).
- **GN 653.2-NI**: AISI 303 stainless steel, sandblasted matte finish.

FEATURES AND APPLICATIONS

The retained screws with GN 653.2 knurled grip knob allow the rapid mounting of machine parts (machine protections, latches, etc.) remaining fastened in the mobile part without risk of loss.



GN 653.2-ST

Code	Description	d1	d2	d3	d4-0.2	d5	l1	l2	l3	h	k	a1	a2	a3	△
GN.28005	GN 653.2-M4-15-ST	M4	16	8	3.2	4.5	15	5	2	5.5	3.5	2+4	4+8	8+10	7
GN.28015	GN 653.2-M4-17-ST	M4	16	8	3.2	4.5	17	5	2	5.5	3.5	4+6	6+10	10+12	8
GN.28025	GN 653.2-M4-19-ST	M4	16	8	3.2	4.5	19	5	2	5.5	3.5	6+8	8+12	12+14	9
GN.28033	GN 653.2-M4-21-ST	M4	16	8	3.2	4.5	21	5	2	5.5	3.5	8+10	10+14	14+16	10
GN.28037	GN 653.2-M5-18-ST	M5	20	10	4	5.5	18	6	2.5	6.5	4	2.5+4	4+10.5	10.5+12	13
GN.28041	GN 653.2-M5-20-ST	M5	20	10	4	5.5	20	6	2.5	6.5	4	4+6	6+12	12+14	14
GN.28045	GN 653.2-M5-22-ST	M5	20	10	4	5.5	22	6	2.5	6.5	4	6+8	8+14	14+16	15
GN.28049	GN 653.2-M5-26-ST	M5	20	10	4	5.5	26	6	2.5	6.5	4	8+12	12+16	16+18	16
GN.28053	GN 653.2-M6-24-ST	M6	24	12	4.8	6.5	24	8	3	8	5	3+6	6+13	13+16	23
GN.28057	GN 653.2-M6-26-ST	M6	24	12	4.8	6.5	26	8	3	8	5	6+8	8+16	16+18	24
GN.28061	GN 653.2-M6-30-ST	M6	24	12	4.8	6.5	30	8	3	8	5	8+12	12+18	18+22	25
GN.28065	GN 653.2-M6-34-ST	M6	24	12	4.8	6.5	34	8	3	8	5	12+16	16+22	22+26	27

Clamping elements