



Note:
 RoHS 2.0 AND REACH Compliant
 Test:
 Grade Designation: Each to Reference

Type	Multi-Mode
Insertion Loss	≤ 0.2dB
Return Loss	≤ 25dB
Test Wavelength	850nm

MATERIAL LIST:

NO.	SPECIFICATION STANDARD	QT' Y	REMARK
⑫	LC Dust Cap White	2pcs	
⑪	LC/UPC MM Ceramic Ferrule	2pcs	
⑩	LC Beige Duplex Clip	1pcs	
⑨	LC Duplex Connector Beige	2pcs	
⑧	LC 3.0 Boot White	2pcs	
⑦	LSH 3.0 Boot Red	2pcs	
⑥	Fiber Optical Cable Erika Violet RAL4003 OM4 50/125um Duplex Ø3.0*6.0mm LSZH	L	
⑤	Black Heat Shrink Tube	2pcs	
④	Ring 1、2	4pcs	
③	LSH 3.0 Boot Black	2pcs	
②	LSH Connector Beige	2pcs	
①	LSH Metal Dust Cap	2pcs	

ITEM NO.	DESC.
21.15.9470	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 0.5m
21.15.9471	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 1m
21.15.9472	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 2m
21.15.9473	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 3m
21.15.9475	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 5m
21.15.9476	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 7.5m
21.15.9477	ROLINE FO Jumper Cable LSH-LC Duplex, 50/125um, OM4, 10m

NO.	SPECIFICATION STANDARD	QT' Y	REMARK
	NEW	2018-05-07	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE

