

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190380001](#)
Status: **Active**
Overview: [Snap Plugs and Receptacles](#)
Description: InsulKrimp Snap Plug Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Documents:

[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Quick Disconnects
 Series [19038](#)
 Comments Fits Male Plug size 3.96mm
 Crimp Quality Equipment Yes
 Insulated Fully
 Overview [Snap Plugs and Receptacles](#)
 Product Name InsulKrimp
 Type Snap Receptacle
 UPC 800753048621

Physical

Barrel Type Closed
 Color - Resin Red
 Flammability 94V-0
 Gender Female
 Glow-Wire Capable No
 Insulation PVC
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin PVC
 Net Weight 1.041/g
 Orientation Straight
 Packaging Type Bag
 Plating min - Mating 4.064µm
 Plating min - Termination 4.064µm
 Tab Thickness N/A
 Tab Width N/A
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.25mm max.
 Wire Size AWG 18, 20, 22

Electrical

Voltage - Maximum 600V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number BRA-2156



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19038 Series](#)

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

SD-19038-001

This document was generated on 09/20/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION