

## Coaxial Cable Connector 24\_BNC-75-4-3/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

Interface compatible with IEC 61169-8



### Technical Data

#### Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0167 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00071754
Catalogue drawing	DCA-00008930
Assembly instruction	DOC-0000179061
Mounting hole	DOU-00008751

### Ordering Information

Single package	24_BNC-75-4-3/133_NE
----------------	----------------------

### Additional Information

Suitable cables	RG_59_B/U, GX_04273
-----------------	---------------------