

Mechanical characteristics

cables

interface dimensions acc. to assembly code

center conductor
outer conductor

mating life

Components

center contact
outer contact
springwasher
other metal parts
insulator
gasket

Electrical characteristics

impedance
frequency
working voltage
voltage proof
insulation resistance
contact resistance
center contact
outer contact

Environmental

operating temp.
protection class
RoHS compliant

Mechanische Eigenschaften

Kabel

Steckgesicht nach Montageanleitung

Innenleiter
Außenleiter

Steckzyklen

Bauteile

Innenkontakt
Außenkontakt
Federscheibe
sonstige Metallteile
Isolierung
Dichtung

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Betriebsspannung
Prüfspannung
Isolationswiderstand
Durchgangswiderstand
Innenkontakt
Außenkontakt

Umgebung

Betriebstemperatur
Schutzklasse
RoHS konform

only for cable with solid inner conductor / nur für Kabel mit massivem Innenleiter

① 1.4/3.8 AF Draka, 7808A Belden, CNT-240 Andrew, HPF 240 Harbour Industries, LMR-240 TMS, MRC 240 AFB Draka, S 04172 D Suhner, SPEEDFOAM 240 HFJ Habia, SX 04172 B-60 Suhner, TZC 500 25 Ericsson, WCX240 NEK/CDT

IEC 60169-17
B98
clamp / klemm
clamp / klemm
>500



Materials / Material

copper alloy/Kupferleg.
brass/Messing
copper alloy/Kupferleg.
brass/Messing
PTFE
silicone/Silikon, NBR

Finish / Oberfläche

NiP Au
Cu2Ni5
Cu2Ni5
Cu2Ni5/CuSnZn

50 Ω
0-11 GHz
≤ 500V_{eff} / 50 Hz
1,5 kV_{eff} / 50Hz
≥ 5 GΩ
≤ 10 mΩ
≤ 2.5 mΩ
-30°C / +85°C
IP 67 (IEC 60529)
2011/65/EU

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name		Datum/ date	Name/ name	Gewicht/ weight [g]
			gez./ drawn	06.12.2016	BJ		
			gepr./ appr.	14.12.2016	KL	ca./approx.	40
Maßstab/ scale				Benennung/ title			
2:1				TNC Straight Plug, field mount type TNC-Kabelstecker, Feldmontage-Type			
untol. Maße/ dim. without tolerances according to				Untert./ doc. type		Zeichnungsnr./ drawing no.	
				K		J01010A0069	
Ersatz für/ replaces							
							
				 Maße/ dimensions: mm			
				Original : DIN A4			
				Blatt/ sheet 1 von/ of 1			