

MOROCCO 1 SIDE

316 STAINLESS STEEL



SPECIFICATIONS

Version	MOROCCO (1 SIDE)
LED type	LED HP
Power (W)	1 W-350mA / 2W-700mA
Driver	Not included
Color temperature	3000K
Real lumens (lm)	50/100
Finishes	Stainless Steel
Measures (mm)	Ø37x59
Cutout hole (mm)	concrete Ø37x90, decking Ø34
Weight (Kg)	0.13
Body	Stainless Steel 316
IP	IP67
IK	IK08
Temperature range	-20°C +50°C



ACCESSORIES




Driver 350mA 1-4W
IP65 On-Off 100-240V
Ref. 4.1011.1301




Driver 700mA 1-4W
IP65 On-Off 100-240V
Ref. 4.1031.1302




Driver ON-OFF 700mA
3W 100-240V IP65
Ref. 4.1013.1303



Driver ON-OFF EU
350mA 1-8W 100-
240V IP54
Ref. 4.3041.1201




Driver ON-OFF EU
700mA 6W 100-240V
IP54
Ref. 4.3043.1201



DETAILS



PVC Recessed box
included



Make correct drainage
(min. 300 mm.)