

Product data sheet

Item No. 92.207.5004.1

Cable assembly GST18I4KS-S 15 50SW

geis® Connection cable male - free end; length: 5m; type GST18I4; 4-pole; 250/400 V / 16 A; colour of coding: black with black strain-relief; cable: H05VV-F 4G1,5, colour: black



Item No.	92.207.5004.1
EAN	4015573569232
Order Unit	10 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	4
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F

Cable colour	Black
Cable diameter	9.2 mm
Version of cable	Male - free end
Type of cord set	Connection cable
Version cable end 1	GST18i4 plug
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	5 m
--------------	-----

Technical drawing

Here dimensions will be reported inside of drawings
 Hier werden die Dimensionen angegeben
 Here dimensions will be reported inside of drawings
 Hier werden die Dimensionen angegeben

Kabel/cable: H05VV-F4G1,5
 Farbe/colour: siehe Tabelle/see table

Stecker/teil/male connector

Kabel/cable: H05VV-F4G1,5
 Farbe/colour: siehe Tabelle/see table

Pol	Aderfarbe
pole	colour of core
L2	schwarz / black
N	blau / blue
⊕	grün-gelb / green-yellow
L1	braun / brown

.F	Farbe	Codierung	Kabelfarbe / cable colour
	colour	*X* Stecker	Zugentlastungsfarbe/strain relief colour
.1	schwarz	1 PE N 2	schwarz
.2	weiß		weiß
.3	grau	1 PE N 2	schwarz
			black

Teile-Nr.	L	Beispiel (Farbe: schwarz)	Typ
part-no.		example (colour: black)	type
92.207.XX04.F	XX in dm-Schritten	92.207.1004.1 = 10dm/L = 1000mm	GST18i4KS-S 15 10SW
U2.207.XX04.F	XX in m-Schritten	U2.207.1204.1 = 12 m/L=12000mm	GST18i4KS-S 15 X10SW

Weitere Daten siehe Katalog
 further data see catalog

Typ/type: GST18i4KS-S 15 .. SW = schwarz/black
 .. WS = weiß/white
 GR01 = grau/grey

Werkstoff/Material: ZN/Cu, 14.05, System I, T
 Zeichnung Nr./Drawing No.: 92.207.0504.1 01K e

PRE-ASSEMBLED CABLE
 KONFEKT-LEITUNG
 Stecker/male - freies Ende/free end 1,5mm
 Schraubanschluß/screw connection 250V