

SVJB clamp holder, positive, right

For copy, longitudinal and face turning with VB indexable insert

ATORN[®]

Application


For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVJBR 1212 F11

Advantage

- Very streamlined geometry, optimised for contour lathe work
- Positive geometry for the body ensures low cutting forces
- Very good surface quality for medium infeed and finishing



| | |
|---------------------------------------|-------------------|
| Art. no. | 17836 320 |
| ISO name | SVJB R/L 1212 F11 |
| Shaft height | 12 mm |
| Shank width | 12 mm |
| Length | 80 mm |
| Length of head | 21.5 mm |
| Programming size | 16 mm |
| Suitable for indexable inserts | VB.. 1103.. |
| Tool design | Right |

EAN-Code

4050293563450