

## Electronic depth callipers

IP67 with integrated EWRI wireless transmission, incl. 3 replaceable gauge slides



### Application:

For universal measurement of depth, width, steps and distance dimensions.

### Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function
- Preset function

### Advantage:

- Key lock to prevent unintentional adjustment
- Switched on automatically by moving the slider
- Unrestricted freedom of movement (radio range up to 6 m)

### Delivery:

In a case with battery (1 x 3 V lithium type CR 2032)



<b>Art. no.</b>	<b>31285 511</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4126513
<b>Min./max. length measuring range</b>	0-100 mm
<b>Data transmission type</b>	multiCOM
<b>Digit increment</b>	0.01 mm
<b>Error limit</b>	0.03 mm
<b>IP protection class</b>	IP 67
<b>Bridge length x bridge width</b>	85 x 8 mm
<b>Type of locating</b>	With locking screw
<b>Calibration Group</b>	B
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Display</b>	Digital
<b>Battery designation</b>	3V CR2032 Lithium
<b>ISO</b>	13385-2
<b>Bridge length</b>	85 mm
<b>Gross Weight</b>	0.600 kg
<b>Product Group</b>	305

### EAN

4059192059095