

Electronic 3-point internal micrometer

Digital ABS Borematic

Mitutoyo

Application:

For measuring through-bores and short centring shoulders in series production.

Execution:

- LCD display, 11 mm high
- Titanium coated
- GO/NG tolerance judgement function
- Preset function
- ON/OFF
- Digimatic
- ABS function
- HOLD function
- Tolerance display
- Locking function

Advantage:

- Quick and easy measurement. Suitable for series measurements
- 330° rotating display unit allows easy reading at any working angle

Delivery:

Includes box, key, battery, factory test certificate



Art. no.	32017 759
Brand	MITUTOYO
Manufacturer Part Number	568-463
Min./max. length measuring range in inches	0.425-0.5 in
Data transmission type	DIGIMATIC
Digit increment	0.00005 in
Design	Metric, Imperial
Error limit	0.00025 in
Digit height	11 mm
Display	Digital
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
Calibration Group	I
Gross Weight	1.835 kg
Product Group	3MA

EAN

4946368636467