

electronic pocket vernier calipers

Digital ABS AOS vernier caliper

Mitutoyo

Application:

For measuring external, internal, step and depth dimensions.

Execution:


- ON/OFF
- Zero setting at any position
- ORIGIN
- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- AOS (advanced on-site sensor) magnetic-inductive scale
- No influence on the measurement due to contamination of the scale (dust, oil, water etc.).
- Smooth and stable guide surfaces

Delivery:

Delivered in box



Art. no.	32018 025
Brand	MITUTOYO
Manufacturer Part Number	500-205-30
Min./max. length measuring range	0-300 mm
Data transmission type	DIGIMATIC
Depth gauge rod	Flat
With drive wheel	No
Error limit	0.03 mm
Length of jaw	64 mm
Design	Metric
Digit height	11 mm
Length of cross tips	22 mm
Digit increment	0.01 mm
Type of locating	With locking screw
Preset function	No
With mm / inch switching	No
Length	404 mm
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	ABS function, Absolute function, Origin (Dimension preset), On/Off
Gross Weight	0.786 kg
Product Group	3MA

EAN

4946368728384