

## Micrometer

Narrow measuring surfaces

Mitutoyo

### Application:

For measuring narrow external recesses.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces or hardened blades
- Friction coupling for consistent, repeatable measuring force
- Non-rotating measuring spindle

### Advantage:

- Accesses hard-to-reach measuring points

### Delivery:

Includes box, adjustment wrench



|  |                  |
|--|------------------|
| <b>Art. no.</b>  | <b>32116 543</b> |
| <b>Brand</b>   | MITUTOYO         |
| <b>Manufacturer Part Number</b>                          | 122-105-10       |
| <b>Min./max. length measuring range</b>                  | 100-125 mm       |
| <b>Vernier scale</b>                                     | 0.01 mm          |
| <b>Measuring surface depth</b>                           | 6.5 mm           |
| <b>Measuring spindle increments</b>                      | 0.5 mm           |
| <b>Bracket depth</b>                                     | 94 mm            |
| <b>Measuring surface width x Measuring surface depth</b> | 0.75 x 6.5 mm    |
| <b>Spindle clamping</b>                                  | No               |
| <b>Error limit</b>                                       | 4 µm             |
| <b>Display</b>   | Nonius           |
| <b>Min./max. measurement force</b>                       | 3-8 N            |
| <b>Calibration Group</b>                                 | D                |
| <b>Gross Weight</b>                                      | 0.670 kg         |
| <b>Product Group</b>                                     | 3MA              |

### EAN

4946368847351