

Precision scales 572

robust metal housing, bestseller for many applications

KERN

Application:

Versatile applications; suitable for use e.g. as laboratory scales, counting scales or check-weigher scales.

Execution:

- Robust metal housing
- LCD display with 14 mm digit size
- Automatic reference optimisation
- Mechanical overload protection
- Options: Battery operation
- Integrated KERN Universal Port (KUP): Connection of external KUP interface adapters, such as RS-232, USB, Bluetooth, Wi-Fi or Ethernet. (Adapter not included in scope of delivery.) This means that interfaces may easily be retrofitted without the need to open the scale housing and without complicated installation
- KERN Communication Protocol (KCP): The KCP allows for placing queries and remote control of the scale via external control units or computers

Advantage:

- User-programmable weighing unit (thread length g/m, paper weight g/m²)
- 572 model series scales can be integrated into the KERN Easy Touch system.

Delivery:

Mains adapter



Art. no.	44615 030
Brand	KERN
Manufacturer Part Number	572-49
Type description	572-49
Max. weight measuring range	16100 g
Digit increment, weight	0.1 g
Plate size	160 x 200 mm
With unit counting	Yes
Min. item weight	0.3 g
Reproducibility	0.1 g
Linearity	0.3 g
Data transmission type	RS232
Housing dimensions (LxWxH)	310 x 180 x 90 mm
Gross Weight	4.202 kg
Product Group	447

EAN

4045761014350