

## Mobile workbench with manual height adjustment

Solid beechwood 1500 mm, 2 drawers with full extension, height-adjustable by crank handle

### Execution:

- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet
- Runs on 2 steering rollers and 2 fixed castors
- Steering rollers with wheel block

### Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- always working at the right height ensures ideal ergonomic conditions
- Running gear makes workbench suitable for mobile use
- When you buy this product, you plant a tree and also receive a tree certificate!

### Delivery:

Fully assembled including hand crank



<b>Art. no.</b>	<b>50212 381</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50212381
<b>Number of drawers</b>	2
<b>Worktop width</b>	1500 mm
<b>Worktop height</b>	50 mm
<b>Pullout type</b>	Full extension
<b>Worktop depth</b>	700 mm
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Functions</b>	RFID possible
<b>Max. height</b>	1040
<b>Min. height</b>	740
<b>Adjustable in height</b>	Yes
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>With single pull-out safety brake</b>	Yes
<b>Surface</b>	Powder-coated
<b>Load-carrying capacity</b>	800 kg
<b>Drawer front height</b>	1 x 150 mm, 1 x 180 mm
<b>Type</b>	Manual height adjustment
<b>Material of worktop</b>	Solid beech
<b>Material of base frame</b>	Steel plate
<b>Drawer width (inner dimension)</b>	450
<b>Drawer depth (inner dimension)</b>	600
<b>Levelling</b>	Yes
<b>Load-carrying capacity per drawer</b>	70 kg
<b>Central locking</b>	No
<b>Gross Weight</b>	115.000 kg
<b>Product Group</b>	5BC

### EAN

4053625402809