


Micro Standard S20 and Stainless S40(W4)



S20



S40



Micro extends our product range for small hose dimensions where a small and flexible wormgear clamp is needed and where the demand for tightening force is low. The band width is 5 mm and the clamp a "retaining" product.

Micro S20: Screw and housing: Electro zinc plated. Band: SS 2320/AISI 430 Stainless Steel.

Micro S40(W4): Screw and housing in stainless AISI 304. Band: SS 2333/AISI 304.

Clamping range (d) mm	Rec. max tightening torque Nm
7 - 11	1,0
9 - 14	
10 - 19	