

TPP1-C1

Mini pocket thermometer with immersion probe

Functions

- Temperature measurement with integrated NTC sensor
- Compact design
- With protective sleeve/holder (TPP1-C1 only)

Product information

- Immersion probe
- Measurement memory (data hold)



TPP1-C1
Article no. 2826634

TPP2-C1

Mini pocket thermometer with surface probe

As TPP2-C1, but with:

- Surface probe without protective sleeve

Technical specifications

Display	LCD, 3½ digit	
Measurement range	-50 to +250°C	
Range	Resolution	Accuracy
-50...+20° C	1° C	±3° C
-19.9 ... +49.9° C	0.1° C	±2° C
+50.0 ... +199.9° C	0.1° C	±(3 % rdg. + 1° C)
+200 ... +250° C	1° C	±(3 % rdg. + 1° C)
Temperature change/response time	> 5 K/s	
Probe dimensions		
TPP1-C1	128 mm x Ø 3.8 mm	
TPP2-C1	125 mm x Ø 13.7 mm (tube Ø 3.8 mm)	
Power supply	1x battery 3 V, IEC 2032	
Dimensions (with protective sleeve):	approx. 40 x 30 x 160 mm	
Weight	approx. 16 g	

Included: 1x TPP1-C1 or TPP2-C1, 1x Battery 3 V, IEC 2032, 1x User manual



TPP2-C1
Article no. 2826652



Heat-conducting paste up to 250 °C (30 g) Model 1032
Article no. 2145689

TH-1

Digital humidity and temperature meter

Functions

- Humidity measurement
- Temperature measurement
- Integrated measurement memory (data hold)
- MIN and MAX data hold
- Auto Power Off
- Measurement of wet bulb temperature

Product information

- Probe integrated in device
- Switchable between °C and °F measurement
- Compact and handy design
- Dew point measurement

Technical specifications

Display	Dual LCD
Humidity measurement	
Measurement range	0 to 100% rel. humidity
Resolution	0.1%
Accuracy	± 3% rel. humidity
Temperature measurement	
Measurement range	-20 to +50°C / -4 to +122°F
Resolution	0.1°C / 0.1°F
Accuracy	± 0.6°C / ± 1°F
Power supply	1x battery 3V, CR2032
Dimensions	175 x 42 x 16 mm
Weight	approx. 120 g

Included: 1x TH-1, 1x Battery 3 V, CR2032, 1x User manual



TH-1
Article no. 3311871