

Datasheet

Art.No. F0.000.0037.4

antenna WIENET ANTENNE 15854 WIFI MAGNET ANT.

"wienet Wireless magnetic base. WLAN / WIFI / Bluetooth / Zigbee Frequency range: WLAN / WiFi: 2.4 GHz Gain: 4.8 dBi Polarization: Vertical Resistance: 50 Ohm WIFI connector: SMA / M-RP Temperature range: -40 to 85 ° C Cable Length: 2500 mm Cable: RG 174 Dimensions: 223 x 29 mm"



Art.No.	F0.000.0037.4
EAN	4049088328121
Order unit	1 pieces

Approvals

Technical data

Classification

ECLASS 8.1	19070105: Wireless Antenna
ETIM 5.0	EC001698: Wireless Antenna