

## Product MD 577 G2

5 mm LED indicator  
 color green

product-catalog	5 mm LED indicator
color	red
part no	MD 577 G2
forward current [mA]	12-16
forward voltage typ. [V]	12-14
wavelength [nm]	565
rec. mounting hole $\varnothing$ [mm]	6.35
panel thickness [mm]	1 .. 3
operating temperature [°C]	-25 .. +80
storage temperature [°C]	-30 .. +85

chip construction	GaP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	25

Low cost LED indicator with ribbed nylon body for easy front panel mounting

150 mm PVC leads \*, AWG 26, red lead, cathode lead = blue  
 \* for special lead length add appendix -Lxxx (xxx length in mm) to standard P/N

### note

- all dimension are in millimeter
- tolerance is  $\pm 0.25$  mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

