







# PROFESSIONAL ELECTRONICS / BUTTON CELLS

ALKALINE / SILVER BATTERIES D-GB-F-I-PL-RUS



LITHIUM BATTERIES D-GB-F-I



Type	CR 2032*	CR 2032*	CR 2032*	CR 2025*	CR 2025*	CR 2025*
IEC	CR 2032	CR 2032	CR 2032	CR 2025	CR 2025	CR 2025
Order-No./ consumer unit	06032 101 401	06032 101 402	06032 101 415	06025 101 401	06025 101 402	06025 101 415
Order-No./ consumer unit International version	06032 112 401	—	—	06025 112 401	—	—
Batteries/ consumer unit	1	2	5	1	2	5
Width (mm) Blister	56	80	80	56	80	80
Height (mm) Blister	65	120	120	65	120	120
Depth (mm) Blister	—	7	7	—	7	7
Weight (g) Blister	—	11	20	—	10	18
Minimum pieces/ shipment unit	10	10	10	10	10	10
Innecarton	—	10	10	—	10	10
Mastercarton	100	100	100	100	100	100
Voltage (V)	3.0	3.0	3.0	3.0	3.0	3.0
Electrochemical System	Lithium	Lithium	Lithium	Lithium	Lithium	Lithium
Typical capacity (mAh)	230	230	230	170	170	170
Height (mm) Battery	3.2	3.2	3.2	2.5	2.5	2.5
Diameter (mm) Battery	20	20	20	20	20	20
Weight (g) Battery	3	3	3	2.5	2.5	2.5
Details	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
EAN/GTIN/ consumer unit	 4 008496 127688 2	 4 008496 174646 0	 4 008496 85085 3	 4 008496 127687 5	 4 008496 174642 2	 4 008496 185089 1

\* UL certified. Underwrites Laboratories www.ul.com

INTERNATIONAL VERSION



GENERAL PURPOSE

RECHARGEABLE

PORTABLE POWER

PROFESSIONAL/BUTTON CELLS

LIGHTS AND BULBS

PRODUCT DISPLAY SYSTEMS

ASSORTMENT OVERVIEW











CR 2016*	CR 2016*	CR 2016*	CR 2430*	CR 2430*	CR 2450*	CR 2450*
CR 2016	CR 2016	CR 2016	CR 2430	CR 2430	CR 2450	CR 2450
06016 101 401	06016 101 402	06016 101 415	06430 101 401	06430 101 402	06450 101 401	06450 101 402
06016 112 401	—	—	06430 112 401	—	06450 112 401	—
1	2	5	1	2	1	2
56	80	80	56	80	56	80
65	120	120	65	120	65	120
—	7	7	—	7	—	7
—	9	14	—	13	—	17
10	10	10	10	10	10	10
—	10	10	—	10	—	10
100	100	100	100	100	100	100
3.0	3.0	3.0	3.0	3.0	3.0	3.0
Lithium	Lithium	Lithium	Lithium	Lithium	Lithium	Lithium
90	90	90	300	300	560	560
1.6	1.6	1.6	3	3	5	5
20	20	20	24.5	24.5	24.5	24.5
1.8	1.8	1.8	4	4	6.2	6.2
Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48

# PROFESSIONAL ELECTRONICS / BUTTON CELLS

ALKALINE / SILVER BATTERIES D-GB-F-I-PL-RUS

LITHIUM BATTERIES D-GB-F-I




Type	CR 2320*	CR 1216*	CR 1220*	CR 1225*	CR 1616*	CR 1620*	CR 1632*	CR 1/3 N*
IEC	CR 2320	CR 1216	CR 1220	CR 1225	CR 1616	CR 1620	CR 1632	CR 11108
Order-No./ consumer unit	06320 101 401	06216 101 401	06220 101 401	06225 101 401	06616 101 401	06620 101 401	06632 101 401	06131 101 401
Order-No./ consumer unit International version	—	—	06220 112 401	—	06616 112 401	06620 112 401	06632 112 401	—
Batteries/ consumer unit	1	1	1	1	1	1	1	1
Width (mm) Blister	56	56	56	56	56	56	56	56
Height (mm) Blister	65	65	65	65	65	65	65	65
Depth (mm) Blister	7.5	7.5	7.5	7.5	7.5	7.5	7.5	13.5
Weight (g) Bister	5	3	3	3	4	4	4	6
Minimum pieces/ shipment unit	10	10	10	10	10	10	10	10
Innecarton	10	10	10	10	10	10	10	10
Mastercarton	100	100	100	100	100	100	100	100
Voltage (V)	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
Electrochemical System	Lithium	Lithium	Lithium	Lithium	Lithium	Lithium	Lithium	Lithium
Typical capacity (mAh)	135	25	35	48	55	70	135	170
Height (mm) Battery	2	1.6	2.0	2.5	1.6	2	3.2	10.8
Diameter (mm) Battery	23	12.5	12.5	12.5	16	16	16	11.6
Weight (g) Battery	2.9	0.7	0.8	0.9	1.2	1.2	1.8	3
Details	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
EAN/GTIN/ consumer unit	 4 008496 270835	 4 008496 270705	 4 008496 276899	 4 008496 747047	 4 008496 270989	 4 008496 276936	 4 008496 576234	 4 008496 274147

\* UL certified. Underwrites Laboratories www.ul.com

INTERNATIONAL VERSION



Back of the packaging with international version



V 28 PXL*	V 8 GS/391	V 10 GA	V 10 GS/389	V 11 A	V 12 GA	V 12 GS/386	V 13 GS/357	V 27 A
2 CR 11108	SR 55	LR 54	SR 54	LR 11	LR 43	SR 43	SR 44	LR 27
06231 101 401	04173 101 401	04274 101 401	04174 101 401	04211 101 401	04278 101 401	04178 101 401	04176 101 401	04227 101 401
—	—	04274 112 401	—	—	04278 112 401	—	04176 112 401	—
1	1	1	1	1	1	1	1	1
56	56	56	56	56	56	56	56	56
65	65	65	65	65	65	65	65	65
17	7.5	7.5	7.5	13.5	7.5	7.5	7.5	13.5
11	3	4	4	7	4	4	5	7
10	10	10	10	10	10	10	10	10
10	10	10	10	10	10	10	10	10
100	100	100	100	100	100	100	100	100
6.0	1.55	1.5	1.55	6.0	1.5	1.55	1.55	12.0
Lithium	Silver oxide	Alkaline	Silver oxide	Alkaline	Alkaline	Silver oxide	Silver oxide	Alkaline
170	40	50	85	38	80	105	155	20
25.1	2.1	3.05	3.05	16.5	4.2	4.2	5.4	28.2
13	11.6	11.6	11.6	10.2	11.6	11.6	11.6	8
8.8	0.9	1.1	1.3	4	1.35	1.78	2.33	4.4
Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
4 008496 274154	4 008496 273607	4 008496 297634	4 008496 273614	4 008496 152865	4 008496 273676	4 008496 273638	4 008496 273621	4 008496 747009

GENERAL PURPOSE

RECHARGEABLE

PORTABLE POWER

PROFESSIONAL/BUTTON CELLS

LIGHTS AND BULBS

PRODUCT DISPLAY SYSTEMS









ASSORTMENT OVERVIEW

# PROFESSIONAL ELECTRONICS / BUTTON CELLS

ALKALINE / SILVER BATTERIES D-GB-F-I-PL-RUS

LITHIUM BATTERIES D-GB-F-I



Type	V 28 PX	V 74 PX	V 76 PX	V 625 U	V 4034	V 321	V 329	V 362
IEC	4 SR 44	-	SR 44	LR 9	4 LR 44	SR 65	-	SR 58
Order-No./ consumer unit	04028 101 401	04074 101 401	04075 101 401	04626 101 401	04034 101 401	00321 101 401	00329 101 401	00362 101 401
Order-No./ consumer unit International version	-	-	-	04626 112 401	04034 112 401	-	-	-
Batteries/ consumer unit	1	1	1	1	1	1	1	1
Width (mm) Blister	56	56	56	56	56	56	56	56
Height (mm) Blister	65	65	65	65	65	65	65	65
Depth (mm) Blister	17	17	7.5	7.5	17	7.5	7.5	7.5
Weight (g) Blister	14	17	5	6	13	3	3	3
Minimum pieces/ shipment unit	10	10	10	10	10	10	10	10
Innecarton	10	10	10	10	10	10	10	10
Mastercarton	100	100	100	100	100	100	100	100
Voltage (V)	6.2	15.0	1.55	1.5	6.0	1.55	1.55	1.55
Electrochemical System	Silver oxide	Alkaline	Silver oxide	Alkaline	Alkaline	Silver oxide	Silver oxide	Silver oxide
Typical capacity (mAh)	145	45	145	200	100	16	39	21
Height (mm) Battery	25.2	35	5.4	6.2	25.2	1.65	3.1	2.1
Diameter (mm) Battery	13	16	11.6	16	13	6.8	7.9	7.9
Weight (g) Battery	11.1	14	2.4	3.3	10.4	0.25	0.6	0.4
Details	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
EAN/GTIN/ consumer unit	 4 008496 273911	 4 008496 273591	 4 008496 274062	 4 008496 273683	 4 008496 274055	 4 008496 336630	 4 008496 660209	 4 008496 317011

\* UL certified. Underwrites Laboratories www.ul.com

INTERNATIONAL VERSION



Back of the packaging with international version



V 364	V 371	V 377	V 379	V 390	V 392	V 393	V 394	V 395	V 396
SR 60	SR 69	SR 66	SR 63	SR 54	SR 41	SR 48	SR 45	SR 57	SR 59
00364 101 401	00371 101 401	00377 101 401	00379 101 401	00390 101 401	00392 101 401	00393 101 401	00394 101 401	00395 101 401	00396 101 401
-	-	-	-	-	-	-	-	-	-
1	1	1	1	1	1	1	1	1	1
56	56	56	56	56	56	56	56	56	56
65	65	65	65	65	65	65	65	65	65
7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
3	3	3	3	4	3	4	4	3	3
10	10	10	10	10	10	10	10	10	10
10	10	10	10	10	10	10	10	10	10
100	100	100	100	100	100	100	100	100	100
1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55
Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide
17	30	24	14	80	40	75	56	42	27
2.15	2.1	2.6	2.15	3.05	3.6	5.4	3.6	2.7	2.6
6.8	9.5	6.8	5.8	11.6	7.9	7.9	9.5	9.5	7.9
0.33	0.61	0.39	0.23	1.32	0.69	1.08	1.04	0.75	0.55
Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
4 008496 1317059	4 008496 1317097	4 008496 1317134	4 008496 1317172	4 008496 1317219	4 008496 1317257	4 008496 1679348	4 008496 1336463	4 008496 1317295	4 008496 1746309

GENERAL PURPOSE

RECHARGEABLE

PORTABLE POWER









PROFESSIONAL/BUTTON CELLS









LIGHTS AND BULBS

PRODUCT DISPLAY SYSTEMS

ASSORTMENT OVERVIEW

# WATCH BATTERIES











Type	V 301	V 303	V 309	V 315	V 317	V 319	V 321	V 329
IEC	SR43	SR44	SR48	SR67	SR62	SR64	SR65	—
Order-No./ consumer unit	00301 101 111	00303 101 111	00309 101 111	00315 101 111	00317 101 111	00319 101 111	00321 101 111	00329 101 111
Minimum pieces/ shipment unit	10	10	10	10	10	10	10	10
Innercarton	100	100	100	100	100	100	100	100
Mastercarton	1000	1000	1000	1000	1000	1000	1000	1000
Voltage (V)	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55
Electrochemical System	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide
Typical capacity (mAh)	95	160	70	23	12.5	22,5	16	39
Height (mm) Battery	4.2	5.4	5.4	1.65	1.65	2.7	1.65	3.1
Diameter (mm) Battery	11.6	11.6	7.9	7.9	5.8	5.8	6.8	7.9
Weight (g) Battery	1.78	2.33	1.08	0.4	0.18	0.29	0.25	0.6
Details	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
EAN/GTIN/ consumer unit	 4 400849612453691	 4 400849612454201	 4 400849612454511	 4 400849612455501	 4 400849612456111	 4 400849612456281	 4 400849612458571	 4 400849612458641












Type	V 377	V 379	V 381	V 384	V 390	V 394	V 395	V 397
IEC	SR66	SR63	SR55	SR41	SR54	SR45	SR57	SR59
Order-No./ consumer unit	00377 101 111	00379 101 111	00381 101 111	00384 101 111	00390 101 111	00394 101 111	00395 101 111	00397 101 111
Minimum pieces/ shipment unit	10	10	10	10	10	10	10	10
Innercarton	100	100	100	100	100	100	100	100
Mastercarton	1000	1000	1000	1000	1000	1000	1000	1000
Voltage (V)	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55
Electrochemical System	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide
Typical capacity (mAh)	24	14	45	40	80	56	42	23
Height (mm) Battery	2.6	2.15	2.1	3.6	3.05	3.6	2.7	2.6
Diameter (mm) Battery	6.8	5.8	11.6	7.9	11.6	9.5	9.5	7.9
Weight (g) Battery	0.39	0.23	0.9	0.69	1.32	1.04	0.75	0.5
Details	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
EAN/GTIN/ consumer unit	 4 400849612459321	 4 400849612459491	 4 400849612459561	 4 400849612456421	 4 400849612456801	 4 400849612458261	 4 400849612458331	 4 400849612457651

\* High Drain

# BUTTON CELLS | ASSORTMENT 2016/17



V 335	V 337	V 339	V 341	V 344	V 346	V 362	V 364	V 371	V 373
—	—	—	—	SR42	—	SR58	SR60	SR69	SR68
00335 101 111	00337 101 111	00339 101 111	00341 101 111	00344 101 111	00346 101 111	00362 101 111	00364 101 111	00371 101 111	00373 101 111
10	10	10	10	10	10	10	10	10	10
100	100	100	100	100	100	100	100	100	100
1000	1000	1000	1000	1000	1000	1000	1000	1000	1000
1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55
Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide
6	8.3	11	15	100	9	21	17	30	30
1.25	1.65	1.4	1.45	3.6	1.29	2.1	2.15	2.1	1.65
5.8	4.8	6.8	7.9	11.6	7.9	7.9	6.8	9.5	9.5
0.15	0.13	0.22	0.28	1.49	0.3	0.4	0.33	0.61	0.5
Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
 4 008496 101467	 4 008496 1362110	 4 008496 1245871	 4 008496 1245888	 4 008496 1245901	 4 008496 101481	 4 008496 1245727	 4 008496 1245734	 4 008496 1245918	 4 008496 1245925

V 350*	V 357*	V 361*	V 370*	V 386*	V 389*	V 391*	V 392*	V 393*	V 396*	V 399*
SR42	SR44	SR58	SR69	SR43	SR54	SR55	SR41	SR48	SR59	SR57
00350 101 111	00357 101 111	00361 101 111	00370 101 111	00386 101 111	00389 101 111	00391 101 111	00392 101 111	00393 101 111	00396 101 111	00399 101 111
10	10	10	10	10	10	10	10	10	10	10
100	100	100	100	100	100	100	100	100	100	100
1000	1000	1000	1000	1000	1000	1000	1000	1000	1000	1000
1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55	1.55
Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide	Silver oxide
110	145	20	30	115	81	42	40	75	27	42
3.6	5.4	2.1	2.1	4.2	3.05	2.1	3.6	5.4	2.6	2.7
11.6	11.6	7.9	9.5	11.6	11.6	11.6	7.9	7.9	7.9	9.5
1.49	2.05	0.4	0.6	1.78	1.31	0.9	0.69	1.08	0.55	0.75
Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48	Page 48
 4 008496 1245697	 4 008496 1245710	 4 008496 1261697	 4 008496 1261710	 4 008496 1245659	 4 008496 1245673	 4 008496 1245789	 4 008496 1245796	 4 008496 1245819	 4 008496 1245741	 4 008496 1245772

GENERAL PURPOSE

RECHARGEABLE

PORTABLE POWER

PROFESSIONAL/BUTTON CELLS

LIGHTS AND BULBS

PRODUCT DISPLAY SYSTEMS

ASSORTMENT OVERVIEW




# BUTTON CELLS REFERENCELIST



VARTA Electronics						Other references						
Type	Order-No./ consumer unit	Voltage (V)	Electrochemical System	Diameter (mm)	Height (mm)	Energizer	Duracell	GP Sylva Cell	Kodak	Panasonic	Renata	IEC
CR 1216	06216 101 401	3.0	Lithium	12.5	1.6	CR 1216	PL 216	CR 1216	—	CR 1216	CR 1216	CR 1216
CR 1220	06220 101 401	3.0	Lithium	12.5	2	CR 1220	DL 1220	CR 1220	—	CR 1220	CR 1220	CR 1220
CR 1225	06225 101 401	3.0	Lithium	12.5	2.5	—	—	—	—	—	CR 1225	CR 1225
CR 1616	06616 101 401	3.0	Lithium	16	1.6	CR 1616	DL 1616	CR 1616	—	CR 1616	CR 1616	CR 1616
CR 1620	06620 101 401	3.0	Lithium	16	2	CR 1620	DL 1620	CR 1620	—	CR 1620	CR 1620	CR 1620
CR 1632	06632 101 401	3.0	Lithium	16	3.2	CR 1632	—	—	—	CR 1632	CR 1632	CR 1632
CR 2016	06016 101 401	3.0	Lithium	20	1.6	CR 2016	DL 2016	CR 2016	KCR 2016	CR 2016	CR 2016	CR 2016
CR 2025	06025 101 401	3.0	Lithium	20	2.5	CR 2025	DL 2025	CR 2025	KCR 2025	CR 2025	CR 2025	CR 2025
CR 2032	06032 101 401	3.0	Lithium	20	3.2	CR 2032	DL 2032	CR 2032	KCR 2032	CR 2032	CR 2032	CR 2032
CR 2320	06320 101 401	3.0	Lithium	23	2	CR 2320	—	—	—	CR 2320	CR 2320	CR 2320
CR 2430	06430 101 401	3.0	Lithium	24.5	3	CR 2430	DL 2430	CR 2430	KCR 2430	CR 2430	CR 2430	CR 2430
CR 2450	06450 101 401	3.0	Lithium	24.5	5	CR 2450	DL 2450	CR 2450	KCR 2450	CR 2450	N	CR 2450
CR 1/3 N	06131 101 401	3.0	Lithium	11.6	10.8	2 L 76	DL 1/3 N	CR 1/3N	K 58 L	—	—	CR 11108
V 28 PXL	06231 101 401	6.0	Lithium	13	25.1	—	28 L	—	K 28 L	—	—	2 CR 11108
V 8 GS/391	04173 101 401	1.55	Silberoxid	11.6	2.1	LR 55/191	391	—	—	SR 1120	391	SR 55
V 10 GA	04274 101 401	1.5	Alkaline	11.6	3.05	LR 54/189	LR 54	189	KA 54	LR 1130	—	LR 54
V 10 GS/389	04174 101 401	1.55	Silberoxid	11.6	3.05	390/389	D 389	389E	—	SR 1130	389	SR 54
V 11 A	04211 101 401	6.0	Alkaline	10.2	16.5	A 11/E 11	MN 11	11 A	—	—	—	11 A
V 12 GA	04278 101 401	1.5	Alkaline	11.6	4.2	LR 43/186	LR 43	186	KA 43	LR 43	—	LR 43
V 12 GS/389	04178 101 401	1.55	Silberoxid	11.6	4.2	386/301	D 386/301	386F	—	SR 43	386	SR 43
V 13 GA	04276 101 401	1.5	Alkaline	11.6	5.4	LR44/A 76	LR44	A 76	KA 76	LR 44	LR 44	LR 44
V 13 GS/357	04176 101 401	1.55	Silberoxid	11.6	5.4	357/303	D 357/303	357/F	—	—	357	SR 44
V 23 GA	04223 101 401	12.0	Alkaline	10.3	28.5	A23/E23A/SA23	MN 21	23 AE	—	LRV08	—	3 LR 50
V 27 A	04227 101 401	12.0	Alkaline	8	28.2	A 27	MN 27	27 A	—	—	—	27 A
V 28 PX	04028 101 401	6.2	Silberoxid	13	25.2	544/4SR44/ A544/4LR44	—	476 F/476E	KS 28	4 SR 44	—	4 SR 44
V 74 PX	04074 101 401	15.0	Alkaline	16	35	E 504	M 504	—	KA 74	—	—	10 LR 54
V 76 PX	04075 101 401	1.55	Silberoxid	11.6	5.4	EPX 76	D 357/7	—	KS 76	SR 44	—	SR 44
V 625 U	04626 101 401	1.5	Alkaline	16	6.2	EPX 625 G	625 A	PX 625 A	KA 625	—	—	LR 9
V 4034	04034 101 401	6.0	Alkaline	13	25.2	A 544	4 LR44	476 A	K 28 A	4 LR 44	—	4 LR 44
LR1/4001/N	04001 101 401	1.5	Alkaline	12	30.2	LR1/E 90	N	910 A	KN	LR1	—	LR 1
AAAA	04061 101 402	1.5	Alkaline	8.2	40.2	AAAA	MN 2500	—	—	—	—	LR8D425

VARTA Button cells						Other references								
Type	Order-No./ consumer unit	Voltage (V)	Electrochemical System	Diameter (mm)	Height (mm)	Bulova	Citizen	Maxell, Toshiba	Rayovac, Renata, Philips	Sony	Panasonic	GP	Energizer, Duracell	IEC
V 301	00301 101 111	1.55	Silberoxid	11.6	4.2	226	280-01	SR43SW	301	—	SR43	386E	386/301	SR 43
V 303	00303 101 111	1.55	Silberoxid	11.6	5.4	228	280-08	SR44SW	303/357/01B	—	—	357E, 357F	357/303	SR 44
V 309	00309 101 111	1.55	Silberoxid	7.9	5.4	—	—	SR754SW	—	—	—	—	393/309	SR 48
V 315	00315 101 111	1.55	Silberoxid	7.9	1.65	614	280-56	SR716SW	315	SR716SWN-PB	—	—	315	SR 67
V 317	00317 101 111	1.55	Silberoxid	5.8	1.65	616	280-58	SR516SW	317	SR516SWN-PB	SR516	—	317	SR 62
V 319	00319 101 111	1.55	Silberoxid	5.8	2.7	615	280-60	SR527SW	319	—	—	—	319	SR 64
V 321	00321 101 111	1.55	Silberoxid	6.8	1.65	611	280-73	SR616SW	321	SR616SWN-PB	SR616	—	321	SR 65
V 329	00329 101 111	1.55	Silberoxid	7.9	3.1	—	—	SR731SW	329	SR731SWN-PB	—	—	329	SR 731
V 335	00335 101 111	1.55	Silberoxid	5.8	1.25	622	280-68	SR512SW	335	SR512SWN-PB	—	—	335	SR 512
V 337	00337 101 111	1.55	Silberoxid	4.8	1.65	—	—	SR416SW	337	—	—	—	337	SR 416
V 339	00339 101 111	1.55	Silberoxid	6.8	1.4	—	—	SR614SW	—	—	—	—	339	SR 614
V 341	00341 101 111	1.55	Silberoxid	7.9	1.45	627	—	SR714SW	341	SR714SWN-PB	—	—	341	SR 714
V 344	00344 101 111	1.55	Silberoxid	11.6	3.6	242	—	SR1136SW	344	—	—	—	344/350	SR 42
V 346	00346 101 111	1.55	Silberoxid	7.9	1.29	628	280-66	SR712SW	346	—	—	—	346	SR 712
V 362	00362 101 111	1.55	Silberoxid	7.9	2.1	601	280-29	SR721SW	362	SR721SWN-PB	SR721	—	362/361	SR 58
V 364	00364 101 111	1.55	Silberoxid	6.8	2.15	602	280-34	SR621SW	364	SR621SWN-PB	SR621	364F, 364E	364/363	SR 60
V 371	00371 101 111	1.55	Silberoxid	9.5	2.1	605	280-31	SR920SW	371	SR920SWN-PB	SR920	371F	371/370	SR 69
V 373	00373 101 111	1.55	Silberoxid	9.5	1.65	617	280-45	SR916SW	373	—	—	—	373	SR 68
V 377	00377 101 111	1.55	Silberoxid	6.8	2.6	606	280-39	SR626SW	376/377/01B	SR626SWN-PB	SR626	377F, 377E	377/376	SR 66
V 379	00379 101 111	1.55	Silberoxid	5.8	2.15	618	280-59	SR521SW	379	SR521SWN-PB	SR521	379F	379	SR 63
V 381	00381 101 111	1.55	Silberoxid	11.6	2.1	317	280-27	SR1120SW	381	—	SR1120	—	391/381	SR 55
V 384	00384 101 111	1.55	Silberoxid	7.9	3.6	247	280-18	SR41SW	384	—	SR41	392F, 392E	392/384	SR 41
V 390	00390 101 111	1.55	Silberoxid	11.6	3.05	603	280-24	SR1130SW	390	—	SR1130	389F, 389E	390/389	SR 54
V 394	00394 101 111	1.55	Silberoxid	9.5	3.6	625	280-17	SR936SW	394	SR936SWN-PB	SR936	394F	394/380	SR 45
V 395	00395 101 111	1.55	Silberoxid	9.5	2.7	610	280-48	SR927SW	395	SR927WN-PB	SR927	395F	395/399	SR 57
V 350*	00350 101 111	1.55	Silberoxid	11.6	3.6	604	—	—	—	—	—	—	344/350	SR 42
V 357*	00357 101 111	1.55	Silberoxid	11.6	5.4	228	280-62	SR44W	357	—	SR44	357E	357/303	SR 44
V 361*	00361 101 111	1.55	Silberoxid	7.9	2.1	601	280-53	SR721W	361	SR721SWN-PB	SR721	—	362/361	SR 58
V 370*	00370 101 111	1.55	Silberoxid	9.5	2.1	620	280-51	SR920W	370	SR920SWN-PB	SR920	371F	371/370	SR 69
V 386*	00386 101 111	1.55	Silberoxid	11.6	4.2	260	280-41	SR43W	386/00B	—	SR43	386F	386/301	SR 43
V 389*	00389 101 111	1.55	Silberoxid	11.6	3.05	626	280-15	SR1130W	389/00B	—	SR1130	389F, 389E	390/389	SR 54
V 391*	00391 101 111	1.55	Silberoxid	11.6	2.1	609	280-30	SR1120W	391	—	SR1120	—	391/381	SR 55
V 392*	00392 101 111	1.55	Silberoxid	7.9	3.6	247	280-13	SR41W	392	—	SR41	392F, 392E	392/384	SR 41
V 393*	00393 101 111	1.55	Silberoxid	7.9	5.4	255	—	SR754W	393	—	—	—	393/309	SR 48
V 396*	00396 101 111	1.55	Silberoxid	7.9	2.6	612	280-52	SR726W	396	—	SR726	—	397/396	SR 59
V 397	00397 101 111	1.55	Silberoxid	7.9	2.6	607	280-28	SR726SW	397	—	SR726	—	397/396	SR 59
V 399*	00399 101 111	1.55	Silberoxid	9.5	2.7	613	280-44	SR927W	399	SR927SWN-PB	SR927	395F	395/399	SR 57

\* High Drain



GENERAL PURPOSE

RECHARGEABLE

PORTABLE POWER

PROFESSIONAL/BUTTON CELLS

LIGHTS AND BULBS

PRODUCT DISPLAY SYSTEMS

ASSORTMENT OVERVIEW