

# ARCA 405021

**FIBOX**  
Enclosing innovations



Sample image

**Order symbol:** ARCA 405021

**Product nbr:** 8120025

**Description:** Cabinet, PC


**Remarks:** Grey cover. 2-point locking, hinges on the short side

**Including:** Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate, 3mm double bit lock(s) with key, 5 versions with swinghandle 2-point locking system, Door guide included.

**EAN:** 6418074079367

**El. number:**

- Finland: 3423123
- Denmark: 8212091236
- Sweden: 2500115



| Dimensions: | Height | Width | Depth |
|-------------|--------|-------|-------|
| mm:         | 400    | 500   | 210   |
| inch:       | 15.75  | 19.69 | 8.58  |

#### Materials:

|                  |                      |
|------------------|----------------------|
| Material:        | Polycarbonate        |
| Base colour:     | RAL 7035 -light grey |
| Cover colour:    | RAL 7035 -light grey |
| Gasket material: | Polyurethane         |

#### Temperatures:

|                              |             |
|------------------------------|-------------|
| Temperature °C (short term): | -40 ... 120 |
| Temperature °C (continuous): | -40 ... 80  |
| Temperature °F (short term): | -40 ... 250 |
| Temperature °F (continuous): | -40 ... 175 |

#### Accessories:

|                 |   |
|-----------------|---|
| SBK ARCA 50     | Support bar kit<br>(435 x 40 x 30)  |
| MPX ARCA 5040   | Mounting plate (450x350 mm)<br>(450 x 350 x 5)  |
| MPMP ARCA 5040  | Mounting plate multiperforated (450x350x2 mm - $\varnothing$ 3.6 mm)<br>(450 x 350 x 2) |
| DSP ARCA HRS    | Door stopper ARCA, horizontal, right, small   |
| DRS ARCA 405021 | DIN rail frame set<br>(485 x 385 x 35)  |
| DSP ARCA HLS    | Door stopper ARCA, horizontal, left, small  |
| SBK ARCA 40     | Support bar kit<br>(340 x 40 x 30)  |
| MPP ARCA 4050   | Mounting plate perforated (450x350x2 mm - 26x11 mm)<br>(350 x 450 x 2)                  |
| MPS ARCA 5040   | Mounting plate (450x350x2 mm)<br>(450 x 350 x 2)  |
| PMK ARCA 50     | PoleMounting kit, for pole $\varnothing$ 100-300mm<br>(485 x 385 x 35)                  |
| IDS ARCA 4050   | Inner door set<br>(385 x 285 x 35)  |
| RCS ARCA 4050   | Rain canopy set for size 4050<br>(20 x 500 x 30)  |

#### Rating:

|  |                          |
|--|--------------------------|
| Ingress protection (EN 60529):         | IP66;                    |
| Impact Resistance (EN 62262):          | IK10;                    |
| Electrical insulation:                 | Totally insulated        |
| Halogen free (DIN/VDE 0472, Part 815): | 1                        |
| UV resistance:                         | UL 508                   |
| Flammability Rating:                   | UL 94 5VA                |
| Glow Wire Test (IEC 695-2-1) °C:       | 960 °C                   |
| NEMA Class                             | NEMA 1, 4, 4X, 12 and 13 |

#### Certificates:

Certificate FI 40467