


## P5160

### Pylon Probe

Product Family: Pylon



#### Mechanical:

**Test Center (mil):** 100

**Test Center (mm):** 2.54

**Overall Length (mil):** 1,310

**Overall Length (mm):** 33.27

**Full Travel (mil):** 230

**Full Travel (mm):** 5.84

**Recommended Travel (mil):** 167

**Recommended Travel (mm):** 4.24

#### Thermal:

**Max Operating Temp (°C):** 105

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 8

**Average DC Resistance lower than (mOhm):** 10

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu, Gold plated over hard Nickel

**Barrel Material:** Phosphor Bronze, Gold plated

**Ball Material:** Stainless Steel

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

#### Spring Material

Standard - 2.50 (71.00) - 6.50 (184.00) - Music Wire

Alternate - 1.70 (48.00) - 3.50 (99.00) - Music Wire

Elevated - 2.50 (71.00) - 8.20 (232.00) - Music Wire

#### Body Type

Straight

Pylon Bend

#### Additional information:


Use ARIT-25 tool for installion

## TIPS:

Tip Materials: BeCu, Gold plated, Steel

## Tips:


P5160-1Q




P5160-1R




P5160-1V




P5160-2C




P5160-2W



P5160-3C




P5160-3P




## Related Products:


PR54-0




PR54-0F




PR54-1




PR54-1F




PR54-2




PR54-2F



PR54-3



PR54-3F



ARIT-25

