

ALCATEL-LUCENT ENTERPRISE

Aries 10 Headset

Affordable headset for daily communication

The Alcatel-Lucent Enterprise Aries 10 headset offers a rich communication experience with super light-weight and good quality. Mono and Duo set with different interfaces are suitable for various communication scenarios, large call center, office applications, VOIP applications etc.

Clear voice: high-definition speakers, focus on voice frequency to improve voice quality.

Noise-cancelling: noise cancelling microphone reduces background noise and interference, highlights your voice and improve call quality.




Large earpiece: the headset is designed with large earpiece, aiming to reduce the pressure on your ear.

Super light-weight: mono set < 50g, Duo set < 65g. headset is suitable for long-term wearing.



Features	Benefits
High-definition speaker	Receive a clear speech from the interlocutor
Noise-cancelling microphone	Reduce the impact of background noise to improve call quality
Large earpiece	Reduce the pressure on your ear
Super light-weight	Suitable for long-term wearing
Flexible microphone boom	Improve work efficiency
Different interfaces (RJ 9 or USB-A)	Suitable for various communication scenarios

Product Overview

Connects to	Product	Description	Details	P/N
 Deskphone with RJ9	AH 11 G	Professional Headset, Corded Monaural	Alcatel-Lucent, Polycom, Siemens, HUAWEI	3MK08007AA
	AH 12 G	Professional Headset, Corded Monaural		3MK08008AA
 Deskphone with RJ9	AH 11 GA	Professional Headset, Corded Binaural	Yealink, Grandstream, Avaya	3MK08007AB
	AH 12 GA	Professional Headset, Corded Binaural		3MK08008AB
 PC, Softphone, Deskphone with USB	AH 11 U	Professional USB Headset, Corded	General communication softwares	3MK08009AA
	AH 12 U	Professional USB Headset, Corded Binaural		3MK08010AA

Technical specifications



Product Name	AH 11 G/GA	AH 12 G/GA	AH 11 U	AH 12 U	
Audio	User sound protection	118 dBA SPL	118 dBA SPL	118 dBA SPL	118 dBA SPL
	Speaker size	Ø 28	2pcs Ø 28	Ø 28	2pcs Ø 28
	Speaker Max input power	50mW	50mW	50mW	50mW
	Speaker sensitivity	105±3dB	105±3dB	105±3dB	105±3dB
	Speaker frequency range	100Hz~10KHz	100Hz~10KHz	100Hz~10KHz	100Hz~10KHz
	Microphone type	Noise cancelling	Noise cancelling	Noise cancelling	Noise cancelling
		Uni-Directional	Uni-Directional	Uni-Directional	Uni-Directional
	Microphone sensitivity	-38±3dB@1KHz	-38±3dB@1KHz	-38±3dB@1KHz	-38±3dB@1KHz
Microphone frequency range	100Hz–5KHz	100Hz–5KHz	100Hz–5KHz	100Hz–5KHz	
Ease of use	Intuitive call control unit	No	No	Yes	Yes
Fit & comfort	Headset form factor	Headband	Headband	Headband	Headband
	Boom arm adjustable	330°	330°	330°	330°
	Boom arm flexible	Yes	Yes	Yes	Yes
	Ear cushions	2pcs Foam	4pcs Foam	2pcs Foam	4pcs Foam
Connectivity	Connectivity	Deskphone	Deskphone	USB Deskphone , softphone	USB Deskphone , softphone
	Connection	RJ 9	RJ 9	USB-A	USB-A
	Operating range (cord length)	130cm with the coiled cable	130cm with the coiled cable	240cm	240cm
	Headset bandwidth	wideband	wideband	wideband	wideband
General	Box content	RJ 9 headset, User guide	RJ 9 headset, User guide	USB headset, User guide	USB headset, User guide
	Packaging dimensions (L x W x H)	195*148*42mm	195*148*42mm	195*148*42mm	195*148*42mm
	Weight (incl. cord)	66g	85g	86g	105g
	Certifications	CE, FCC			
	Operating temperature	- 5°C to 45 °C			