

Product information

88 07 250

KNIPEX Alligator®

Water Pump Pliers

DIN ISO 8976 IEC 60900 DIN EN 60900



⚡ 1000 V 



- Good access to the workpiece due to slim size of head and joint area
- More output and comfort compared to conventional water pump pliers of the same length: 9-notch adjustment positioning for 30 % more gripping capacity
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Robust construction, insensitive to dirt; particularly suitable for outdoor work
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

| | |
|-----------------|-------------------------------------|
| Article No. | 88 07 250 |
| EAN | 4003773019343 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | with dipped insulation, VDE-tested |
| Weight | 420 g |
| Dimensions | 250 x 82 x 32 mm |
| Standard | DIN ISO 8976 DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|---------------------------------------|----------|
| Adjustment positions | 9 |
| Capacity for pipes, inches (diameter) | Ø 2 Inch |
| Capacities for nuts | 46 mm |
| Capacities for pipes (diameter) | Ø 50 mm |
| VDE tested | yes |

technical change and errors excepted

