

A fully screened robust range of DIN connectors for use in instrumentation and audio applications. Available in bright nickel plated. Robust construction incorporating cable grip and strain relief.

Manufactured to DIN 41524, 45322, 45326, 45327 and 45329.

Dimensions



Materials		
Housing	Zinc Alloy	
	Heavy Nickel Plated Over Copper	
Moulding	Nylon	
Contacts	Brass Silver Plated	
Cable Clamp	Mild steel Zinc Plated	
Grommet	Black P,V,C	
Electrical		
Rated Voltage	34 V a.c. or d.c.	
Current Rating	2.A	
Test Voltage	500 V r.m.s.	
Insulation Resistance	103 MΩ min at 100 V d.c	
Contact Resistance	10 mΩ max	
Capacitance (mated)	3pF	
Climatic		
Climatic category	25/070/21	
Temperature Range	-25°C to +70°C	
Damp heat, steady state	21 days	



Туре	Deltron No
3 Way	610-0300
4 Way	610-0400
5 Way 45°	610-0500
5 Way 60°	610-0510
5 Way Dice	610-0520
6 Way	610-0600
7 Way	610-0700
8 Way	610-0800



PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF

ALPHA 3 MANUFACTURING.

ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION O

ON IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF INCTURING IS PROHIBITED.

DEM Manufacturing, Delitron Emcon House Hargeroves Way, Sawciffe Ind, Park, Superiores World Incorposition Built Specific Manufacturing and Places 20.125mm ANGULAR TOLERANCE: 21*

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETRES LINEAR TOLERANCE: NO DECIMAL PLACES ±0.5mm 1 DECIMAL PLACE ±0.25mm FINISH SCREENED DIN
CONNECTOR STANDARD
PLUG NICKEL
IF IN DOUBT ASK
DO NOT SCALE DRAWING

MATERIAL

DEBURR AND BREAK SHARP EDGES THIRD ANGLE PRO

SEE NOTE

AX DRAWN BY SPB
APPROVED BY WC
THIRD ANGLE PROJECTION SHEET 1 OF 1
SCALE 1:1
A4

GENERAL SPECIFICATION
FOR
610 SERIES

610 SERIES

Release