

## Adjustable crocodile clamp

With counter-holder



### Application:


The crocodile is used with all clamping tasks where clamping is achieved using T-grooves and tapped holes.

### Execution:

- Tempered and galvanised
- Variable and quick adjustment
- The captive thrust piece and counter-holder are connected to the adjustable clamp (cannot be lost).
- Particularly suitable for use on injection moulding machines and presses
- Accessories facilitate variable adjustment of the clamping height
- Infinitely variable adjustment of clamping height

### Advantage:

- Captive thrust piece connected to the adjustable clamp (cannot be lost), crocodile can therefore be used quickly and flexibly
- Heights are quickly overcome and packing the underside of the adjustable clamp does not present a problem
- Accessories facilitate variable adjustment of the clamping height



<b>Art. no.</b>	<b>26224 030</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	79855
<b>Size</b>	3
<b>Suitable T-groove width</b>	16 mm, 18 mm, 20 mm, 22 mm
<b>Tension force</b>	60 kN
<b>Min./max. adjustment range</b>	0-80 mm
<b>Length</b>	187 mm
<b>Width</b>	62 mm
<b>Height</b>	42 mm
<b>Thickness</b>	27 mm
<b>Bore diameter</b>	21 mm
<b>Gross Weight</b>	2.260 kg
<b>Product Group</b>	260

### EAN

4020772079857