

Sliding door cabinet with doors with viewing window, height 1950 mm

With shelves, load capacity 80 kg per shelf

Execution:

- Stable welded sheet steel structure with base, available in three different heights, widths and depths
- Galvanised shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Sliding doors with reinforcement pockets and recessed handle, guide rail with special rollers and anti-crush protection, cushioned end stops
- Doors can be locked simultaneously with a push and turn cylinder lock, incl. 2 keys

Delivery:

Available on request: DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other paint finishes.

Art. no.	50046 286
Brand	HK
Manufacturer Part Number	50046286
Door design	Inspection glass
Height	1950 mm
Depth	600 mm
Width	2000 mm
With partition wall	Yes
Number of folder height	5 PCS
Number of shelves	8 PCS
Load-carrying capacity per shelf	80 kg
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 450 mm
Drawer front height	150 mm
Load-carrying capacity	600 kg
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	145.000 kg
Product Group	504

EAN

4039247874552