



MASTER - LED HID SON-T



MAS LED SON-T IF 12Klm 65W 740 E40

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER - LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER - LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

Warnings and Safety

• Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	E40		70
Nominal lifetime	70,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	50,000	Photobiological safety according to EN 62471	RG1
Lighting Technology	LED	Operating and Electrical	
Flux measurement reference	Sphere	Line Frequency	50 Hz
Light Technical		Input Frequency	50 Hz
Color Code	740 [CCT of 4000K]	Power Consumption	65 W
Luminous Flux	12,000 lm	Lamp Current (Nom)	1,760 mA
Luminous Efficacy (rated) (Nom)	184 lm/W	Starting Time (Nom)	0.5 s
Color Designation	Cool White (CW)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	-
Color Consistency	<6	Voltage (Nom)	80-90 V
		Inrush current at mains	-

MASTER - LED HID SON-T

Max. lamp no. on MCB B type 10A - Mains	-
Max. lamp no. on MCB B type 10A - EM ballast without Compensation Capacitor.	4
Max. lamp no. on MCB B type 10A - EM ballast with Compensation Capacitor.	8
Max. lamp no. on MCB B type 16A - Mains	-
Max. lamp no. on MCB B type 16A - EM ballast without Compensation Capacitor.	6
Max. lamp no. on MCB B type 16A - EM ballast with Compensation Capacitor.	12
Ballast Compatibility	EM

Temperature

Ambient temperature range	-30 to +45 °C
T-Case Maximum (Nom)	55 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	T70


Approval and Application

Energy Efficiency Class	C
Energy Consumption kWh/1000 h	65 kWh
EPREL Registration Number	1077791
EU RoHS compliant	Yes

Product Data

Order product name	MAS LED SON-T IF 12Klm 65W 740 E40
Full product name	MAS LED SON-T IF 12Klm 65W 740 E40
Full product code	871951444901500
Order code	929003467712
Material Nr. (12NC)	929003467712
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.490 kg
EAN/UPC - Product/Case	8719514449015
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514449022



Dimensional drawing



Product	D	C
MAS LED SON-T IF 12Klm 65W 740 E40	71 mm	262 mm


MASTER - LED SON-T

Photometric data




Light Distribution Diagram - MAS LED SON-T IF 12Klm 65W 740 E40

General uniform lighting - MAS LED SON-T IF 12Klm 65W 740 E40




Spectral Power Distribution Colour - MAS LED SON-T IF 12Klm 65W 740 E40

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LED SON-T IF 12Klm 65W 740 E40

MASTER - LED HID SON-T

