


	REVISED	DR	APP



With the Mini DisplayPort 1.2 cable you connect e.g. your Notebook with a monitor, TV or video projector. A DisplayPort cable transmits digital video and audio signals. This cable supports a maximum resolution of 1920 x 1080 with 60 Hz.


- Connections: Mini DisplayPort plug to DVI 24+1 plug
- Resolution up to: 1920 x 1080 (60Hz)
- DisplayPort Version: 1.2
- Backwards compatible Versions: 1.1
- DVI Version: Digital (Dual Link)

- Material cable sheath: PVC
- Plug: gold plated
- Contact surface: gold-plated pins
- Plug cover: PVC / ABS
- Kink protection: yes
- Construction cable: AWG 32
- Wire material: copper
- Number of shieldings: 3
- Shielding 1: ALU foil laminated PIMF (100% density)
- Shielding 2: ALU foil (100% density)
- Shielding 3: ALU braid
- Color: black

NOTES:

- 1:100% short,open and miss wire test.
- 2:Resolution:1080P,60HZ.
- 2:CABLE MARKING:DisplayPort Cable E***** AWM STYLE 20276 80°C 30V VW-1

PIN OUT



! WORKS IN ONE DIRECTION ONLY, MINI DISPLAYPORT SOURCE (PC) - DVI SINK (DISPLAY) !

NO.	MATERIAL	DESCRIPTION	QTY.	UNIT
⑦	OUTER MOULDED	BLACK 45P PVC	0.048	KG
⑥	INNER MOULDED	LDPE	0.024	KG
⑤	SCREW	#4-40UNC 2.3*45.5MM,BLACK PVC	2	PCS
④	HOUSING	ABS HOUSING FOR MDP,BLACK	1	PCS
③	CONNECTOR	MINI DISPLAYPORT MALE,WHITE INSULATOR,GOLD PLATED PIN AND SHELL	1	PCS
②	CONNECTOR	DVI 24+1 MALE WITH PCB BOARD,BLACK INSULATOR,GOLD PLATED PIN AND SHELL	1	PCS
①	CABLE	(1P*32AWG+D+FAM)*5C+5C*32AWG+AL+D+B,JACKET:BLACK PVC,OD:4.8±0.2MM.	L	M



DESCRIPTION		MINI DP PLUG 1.2 - DVI-D (24+1) PLUG					
SIZE	A4	DATE		CHECKED		TOL	BS10-55025
UNIT	MM	DRAWN		APPROVED			
CUSTOM TARIF NO.: 8517 69 90 000							