

HSK-standard cable glands

HSK-K

NPT

RoHS



Material Polyamide VO according to UL 94

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005), blue (RAL 5012) for the intrinsic safety "i"



- Advice:**
- With additional pre-assembled O-Ring upon request
 - Please find suitable O-Ring on page 88
 - Other sealing material e.g. Silicone upon request
 - Other colors on request



AG	∅k mm	GL mm	H mm	∅ mm	Number grey	Number black	Number blue
NPT 3/8"	4 – 8	15	22	19 / 22	1.209.3800.70	1.209.3801.70	1.209.3802.70
NPT 3/8"	2 – 6	15	22	19 / 22	1.209.3800.71	1.209.3801.71	1.209.3802.71
NPT 1/2"	6 – 12	13	27	24	1.209.1200.70	1.209.1201.70	1.209.1202.70
NPT 1/2"	5 – 9	13	27	24	1.209.1200.71	1.209.1201.71	1.209.1202.71
NPT 1/2" (16)	10 – 14	13	28	27	1.209.1216.70	1.209.1217.70	1.209.1218.70
NPT 1/2" (16)	7 – 12	13	28	27	1.209.1216.71	1.209.1217.71	1.209.1218.71
NPT 3/4"	13 – 18	14	31	33	1.209.3400.70	1.209.3401.70	1.209.3402.70
NPT 3/4"	9 – 16	14	31	33	1.209.3400.71	1.209.3401.71	1.209.3402.71
NPT 1"	18 – 25	19	39	42	1.209.1000.70	1.209.1001.70	1.209.1002.70
NPT 1"	13 – 20	19	39	42	1.209.1000.71	1.209.1001.71	1.209.1002.71
NPT 1 1/4"	18 – 25	16	39	42 / 46	1.209.5400.70	1.209.5401.70	1.209.5402.70
NPT 1 1/4"	13 – 20	16	39	42 / 46	1.209.5400.71	1.209.5401.71	1.209.5402.71
NPT 1 1/2"	22 – 32	20	48	53	1.209.6400.70	1.209.6401.70	1.209.6402.70
NPT 1 1/2"	20 – 26	20	48	53	1.209.6400.71	1.209.6401.71	1.209.6402.71

➔ Accessories see page 73