

## Specifications:

|                              |   |
|------------------------------|---|
| <b>Shell plating:</b>        | Steel tin-plated                        |
| <b>Pin contact:</b>          | Phosphor bronze gold plated over nickel |
| <b>Temperature:</b>          | -55°C to +105°C                         |
| <b>Current rating:</b>       | 5 Amp                                   |
| <b>Dielectric strength:</b>  | 1000V for 1 minute                      |
| <b>Insulator resistance:</b> | 1000MΩ min. @ 500Vdc                    |



| Order code | Description                    | Male/Female | A     | B     | C     | D     |
|------------|--------------------------------|-------------|-------|-------|-------|-------|
| 15-0400    | 15-way High Density 'D' Plug   | M           | 30.81 | 24.99 | 16.92 | 19.28 |
| 15-0405    | 15-way High Density 'D' Socket | F           | 30.81 | 24.99 | 16.33 | 19.28 |
| 15-0410    | 26-way High Density 'D' Plug   | M           | 39.14 | 33.32 | 25.25 | 27.51 |

