



INSTA CONTACTOR 0/1 AUTOMATIC WITH 4 NO CONTACTS CONTACT FOR AC 230, 400V 25A ACTIVATION AC230V DC220V

Figure similar

Model		
product brand name		SENTRON
Product designation		Insta contactors
Protection class		
Protection class IP		IP20
Dissipation		
Active power loss		
<ul style="list-style-type: none"> for rated value of the current / with AC / in hot operating state / per pole 	W	2.2
Main circuit		
Operating voltage / Rated value		
<ul style="list-style-type: none"> minimum 	V	400
<ul style="list-style-type: none"> maximum 	V	400
Operating current / Rated value	A	25
Control current		
Control supply voltage / Rated value	V	230
<ul style="list-style-type: none"> maximum 	V	230
Product details		
Product component / Slide for manual operation		Yes
Product expansion / can be installed / supplementary devices		Yes
Number		
Number of NC contacts		4

Number of NO contacts		0
-----------------------	--	---

Mechanical Design

Height	mm	90
Width	mm	35
Depth	mm	71
Installation depth	mm	64
Number of width units		2

Certificates

Equipment marking / acc. to DIN EN 61346-2		Q
--	--	---

General Product Approval	Declaration of Conformity
---------------------------------	----------------------------------



[other](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5TT50306>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5TT50306/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT50306

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015