

## Product information

# 03 01 250

## Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General	
Article No.	03 01 250
EAN	4003773015222
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	480 g
Dimensions	250 x 48 x 17 mm
Standard	DIN ISO 5746
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 15.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm <sup>2</sup>

*technical change and errors excepted*