

## Sheet metal punches, Tristar

12.5 to 63 mm



### Application:

For punching holes in sheet metal.

### Version:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

### Advantage:

- The sheet does not jam in the centre thanks to the triple partition

### Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



<b>Art. no.</b>	<b>53829 162</b>
<b>Diameter</b>	16.2 mm
<b>Suitable for max. sheet metal thickness</b>	2 mm
<b>Screw diameter</b>	9.5 mm
<b>Screw length</b>	50 mm

### EAN-Code

4030266122679