

# Heat shrink insulated ring terminals




## FEATURES:

Coated with hot-melt adhesive on the inside

## SPECIFICATION:

Material	Copper
Surface material	Tin-plated
Max. temperature	+105 °C



## PRODUCT RANGE:

Article Nr.	Cross-section	AWG	Colour	A	B	Length	Stud Size
RND 465-00639	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	4.3 mm	8.0 mm	26.5 mm	#8
RND 465-00640	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	3.7 mm	5.5 mm	22.2 mm	#6
RND 465-00641	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	5.3 mm	8.0 mm	26.5 mm	#10
RND 465-00642	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	6.4 mm	11.6 mm	32.2 mm	1/4
RND 465-00643	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	8.4 mm	11.6 mm	32.2 mm	5/16
RND 465-00644	0.5...1.5 mm <sup>2</sup>	22-16 AWG	Red	10.5 mm	13.7 mm	36.2 mm	3/8
RND 465-00645	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	3.7 mm	6.6 mm	24.9 mm	#6
RND 465-00646	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	4.3 mm	8.5 mm	27.3 mm	#8
RND 465-00647	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	5.3 mm	9.5 mm	27.2 mm	#10
RND 465-00648	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	6.4 mm	12 mm	31.7 mm	1/4
RND 465-00649	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	8.4 mm	12 mm	31.7 mm	5/16
RND 465-00650	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	6.4 mm	12 mm	39 mm	1/4
RND 465-00651	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	4.3 mm	9.5 mm	32.7 mm	#8
RND 465-00652	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	5.3 mm	9.5 mm	32.7 mm	#10
RND 465-00653	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	8.4 mm	15 mm	41.2 mm	5/16
RND 465-00654	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	10.5 mm	15 mm	41.2 mm	3/8
RND 465-00655	4...6 mm <sup>2</sup>	12-10 AWG	Yellow	13 mm	19.2 mm	46 mm	1/2
RND 465-00681	1.5...2.5 mm <sup>2</sup>	16-14 AWG	Blue	10.5 mm	13.7 mm	36 mm	3/8