



Standard lamps  
Dental technology

For special features, specific benefits and areas of use see page 104



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
00847154	22.8V 75W R7s 13.5x64 clear H018366	22.8	75	3.3	R7s	13.5	64		1,600	1,000			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
00847519	22.8V 150W G6.35 10.7x47 clear transversal	22.8	150	6.6	G6.35	11	47	30.5	4,300	500		S90	
00847518	22.8V 250W G6.35 13x51 clear transversal	22.8	250	11	G6.35	13	53	33	8,000	300		S90	
00847528	22.8V 250W G6.35 13x51 clear transversal	22.8	250	11	G6.35	13	51	33	6,000	1,000		S90	
00847525	24V 150W G6.35 12x47 clear transversal	24	150	6.25	G6.35	11	47	30.5	4,500	300		S90	
00847529	24V 150W G6.35 12x47 clear transversal	24	150	6.25	G6.35	11	47	30.5	3,450	1,000		S90	
00847523	24V 250W GY6.35 16x56 clear transvers.	24	250	10.4	G6.35	16	56	37.5	6,200	1,000		S90	
00847520	22.8V 55W G6.35 10.7X 41 clear transver.	22.8	55	2.4	G6.35	11	41	30.5	1,100	1,000		S90	



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter max. mm	Total length max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
00847521	22.8V 150W G6.35 axial	22.8	150	6.6	G6.35	14	48	32.5	2,800	1,000		S90	
00847524	24V 100W GY 6.35 axial	24	100	4.17	G6.35	12	44	30.5	2,200	1,000		S90	
00847139	24V 120W G6.35 axial	24	120	5	G6.35	11	44	29.9	2,500	800			