


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Fast4
Catalogue number	2943, 2944
Date	19/04/2013

<p>Range Description 4 flute wood drill bits</p> <hr/> <p>Features</p> <ul style="list-style-type: none"> • 4 flute configuration for fast waste removal • 100% more cutting blade than a flat bit or auger • Side blade for clean breakout • Nose screw pulls the bit through – less effort • Clean hole profile • Class leading cutting speeds • 2943 - Fast change docking system (to 25mm) • 2944 – SDS Plus docking system on all sizes 	 <p>2943</p> <p>2944</p>
----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T2943-16	Fast4 wood drill bit 16mm	5013969701821	82075090	10
T2943-20	Fast4 wood drill bit 20mm	5013969701838	82075090	10
T2943-22	Fast4 wood drill bit 22mm	5013969701845	82075090	10
T2943-25	Fast4 wood drill bit 25mm	5013969701852	82075090	10
T2943-32	Fast4 wood drill bit 32mm	5013969701869	82075090	10
T2943S4	Fast4 Bit Set 16, 20, 25 & 32mm	5013969701883	82075090	5
T2944-16	Fast4 SDS+ wood drill bit 16mm	5013969703825	82075090	10
T2944-20	Fast4 SDS+ wood drill bit 20mm	5013969703832	82075090	10
T2944-22	Fast4 SDS+ wood drill bit 22mm	5013969703849	82075090	10
T2944-25	Fast4 SDS+ wood drill bit 25mm	5013969703856	82075090	10
T2944-32	Fast4 SDS+ wood drill bit 32mm	5013969703863	82075090	10

Technical product information	Recommended cutting speeds: 16 – 20mm between 1500 - 2000 RPM 22 – 25mm between 1000 – 1500 RPM 32mm between 800 – 1300 RPM 2943 - Fast change docking system (6.4mm) hex shank provided on sizes up to 25mm Size 32mm has an 11mm hex drive shaft
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship Normal wear and tear of cutting edges and damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T2943-16	16	16	165	65	60	18	250	84
T2943-20	20	20	165	77	60	22	250	96
T2943-22	22	22	165	85	60	24	250	104
T2943-25	25	25	165	97	60	27	250	116
T2943-32	32	32	165	169	60	34	250	188
T2943S4	-	-	-	-	215	35	250	501
T2944-16	16	16	165	98	60	18	250	117
T2944-20	20	20	165	106	60	22	250	125
T2944-22	22	22	165	114	60	24	250	133
T2944-25	25	25	165	122	60	27	250	141
T2944-32	32	32	165	167	60	34	250	186

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T2943-16	145	290	100	978		
T2943-20	145	290	100	1098		
T2943-22	145	290	100	1178		
T2943-25	145	290	100	1298		
T2943-32	145	290	100	2018		
T2943S4	245	290	145	2756		
T2944-16	145	290	100	1308		
T2944-20	145	290	100	1388		
T2944-22	145	290	100	1468		
T2944-25	145	290	100	1548		
T2944-32	145	290	100	1998		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T2943-16	18	Blister	1	Card			138	Box
T2943-20	18	Blister	1	Card			138	Box
T2943-22	18	Blister	1	Card			138	Box
T2943-25	18	Blister	1	Card			138	Box
T2943-32	18	Blister	1	Card			138	Box
T2943S4	85	Blister	8	Card			251	Box
T2944-16	18	Blister	1	Card			138	Box
T2944-20	18	Blister	1	Card			138	Box
T2944-22	18	Blister	1	Card			138	Box
T2944-25	18	Blister	1	Card			138	Box
T2944-32	18	Blister	1	Card			138	Box