

Alubos

Enclosure profiles, open on one side



ABPU 1040-0150

Order no.: 84047150

* = Available on request.

Characteristics

Colour of enclosure group

Black, similar to RAL 9005

Protection class

IP 40

Enclosure Material

Extruded profiles: Al Mg Si 0.5 powder-coated; diecast lid: GB Al Si 12, powder-coated; seal: TPE; for details see Technical Information

Scope of delivery

Enclosure profile. Please order front panel for ABPU separately.

Note


C = profile length, special lengths on request.

Dimensions

Dimensions

108 x 42 x 150 mm

Product drawing



Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary
Product drawing in PDF format: 84047150 ABPU-1040-0150.pdf (84.1 KB)
Product drawing in DXF format: 84047150 ABPU-1040-0150.dxf (3.8 MB)
Drawing for mechanical processing: 84047150 ABPU-1040-0150-G.dxf (275.8 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product information

Alubos GB.pdf (2.7 MB)

Matching accessories



End cover

84041000 ABD 1040

For AB 1040



Mounting lid with hinged aluminium flap

84044000 ABM 1040 SAL

For AB 1040



EMC seals

84200415 DI 1040-EMV

For AB 1040



Seals, ultramarine

84200414 DI 1040-5002

For AB 1040



Seals, fire red

84200411 DI 1040-3000

For AB 1040



Seals, rape yellow

84200412 DI 1040-1021

For AB 1040



Seals, patina green

84200413 DI 1040-6000

For AB 1040



Seals UL 94 V0

84200419* DI 1040-V0

For AB 1040



Wall brackets, sheet steel

84007000 AB-WL2

For AB 1040



Wall brackets, adjustable, sheet steel

84105000 AB-1000 WL V

For AB 1000/1040



Front panels, natural-coloured anodised aluminium

84048150 ABPU 1040-0150 FP2

For ABPU 1040-0150, 2 mm



Mounting clamps

84006510 AB 1040 MKL

For AB 1040



Rubber feet

84006700 AB - GF

Polyurethane, 65-75 Shore

Black