

TY300-50X-100



CBL TIE 50LB 12IN UV BLACK NYLON



General Information

Extended Product Type	TY300-50X-100
Product ID	7TAG054360R0279
EAN	5414363075325
Catalog Description	CBL TIE 50LB 12IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 302.26mm (11.9 Inches), Width of 4.673mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), 100 Pack

Ordering

EAN	5414363075325
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.004 lb
	1.814 g

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	2 in
	51 mm
Package Level 1 Height	6 in
	152 mm
Package Level 1 Depth / Length	16 in
	406 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	13.5 in
	343 mm
Package Level 2 Height	10.25 in
	260 mm
Package Level 2 Depth / Length	17 in
	432 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	3 in 76.2 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Tensile Strength	50 lb 222 N
Thickness	0.049 in 1.24 mm
UPC	786210232249

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY300-50X-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY300-50X-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

