

## MIRO 6.2 IMPULSE EXTENSION MODULES

IN: 24 VDC - OUT: 24 VDC / 0.1 A


Transistor output

Impulse expansion: 0.1...10 s


Screw terminals

### [Link to Product](#)

#### Illustration



OUT Control impuls  $\geq 0.5$  ms  
0.1...10s front side poti adjustable



Product may differ from Image

### Approvals



### Input

Input voltage	19...29 V DC
Control voltage	16...32 V DC
Time range	0.1...10 s
Impulse length	min. 0.5 ms

### General data

Test isolation voltage	no galvanic separation
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C
Dimensions H × W × D	90×6.2×65 mm

### Output

Switching voltage	Operating voltage – 1.5 V
Switching current per output	max. 100 mA

### Commercial data

country of origin	CZ
customs tariff number	85437090
minimum order quantity	1