


BD2A-400-LL-Y*-G* ELBOW LEFT X 0,36M / Y 0,36M-1, 25M 160A-400A WINKEL 85 GRAD-17 5 GRAD



Model

| | |
|---------------------|---|
| Product designation | L unit (junction unit) for BD2 busbar trunking system |
|---------------------|---|

Protection class

| | |
|---------------------|------|
| Protection class IP | IP52 |
|---------------------|------|

Main circuit

| | | |
|--|----|-----|
| Operating frequency / Rated value | | |
| • minimum | Hz | 50 |
| • maximum | Hz | 60 |
| Operating voltage / with AC | | |
| • at 50 Hz / Rated value / maximum | V | 690 |
| • at 60 Hz / Rated value / maximum | V | 690 |
| Operating current | | |
| • for circuit 1 / with AC / at 50 Hz / Rated value / maximum | A | 400 |
| • for circuit 1 / with AC / at 60 Hz / Rated value / maximum | A | 400 |

Connections

| | | |
|--|-----------------|-----|
| Conductor cross section / of the (PE)N | mm ² | 205 |
|--|-----------------|-----|

Mechanical Design

| | | |
|--------------------------|----|----------------|
| Height | mm | 68 |
| Width | mm | 1 250 |
| Mounting type | | ceiling / wall |
| Material / of the busbar | | aluminium |



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/BVP:261872>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/BVP:261872/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=BVP:261872

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

16.03.2015