



Datasheet for part number DBMH17H2SNA197

Our Catalog Part Number: DBMH-17H2S-N-A197
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D

Product Datasheet	
General	Combo D Series: D-Subminiature offering mixed layouts
Wire Gauge Range AWG	AWG 8-26
Mating Cycles	50
Contact Arrangement	17H2 (15 contacts size 20, 2 contacts size 8)
Dielectric Withstanding Voltage	500 VAC at sea level
Current Rating Signal Contacts	7.5 max
Current Rating Size 8 Contacts	40 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	pure tin over nickel
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contact Type	Straight PCB US footprint
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Mounting Method	.300? (7.6mm) Standoff, 4-40 Screwlock