

## Product information

# 98 00 27

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

## Open-end wrench


IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General	
Article No.	98 00 27
EAN	4003773020028
Weight	307 g
Dimensions	57 x 15 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Width across flats	27 mm
Width across flats S	1 Inch
Length l max.	215 mm
Head thickness a max.	9 mm
Head width b max. mm	63 mm



*technical change and errors excepted*

