

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010011024](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: 5.08mm Pitch KK Crimp Terminal Housing, 2 Circuits, Natural

Documents:

[3D Model](#) [Packaging Specification 30010001-PK-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0087-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [3001](#)
 Application Power, Wire-to-Board
 Overview [KK 508 Connector System](#)
 Product Name KK 508
 UPC 800753745537

Physical

Circuits (maximum) 2
 Color - Resin Natural
 Flammability 94V-2
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Nylon
 Net Weight 0.624/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 5.08mm
 Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability WAVE

Material Info

Engineering Number 3001-02

Reference - Drawing Numbers

Packaging Specification 30010001-PK-000
 Product Specification PS-99020-0087-001
 Sales Drawing SDE-3001-N-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3001](#) Series

Mates With

Headers [3061](#) , [3003](#) , [3061](#)

Use With

Crimp Terminals [2478](#) , [2578](#) , [2878](#)