



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Multi-directional head
Product compatibility	XCKL XCKM XCKS

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCKLD39H7 ZCKL5 ZCKLD31 ZCKS7H29 ZCKM7H29 ZCKL5H7 ZCKM7H7 ZCKMD31 ZCKLD39 ZCKS9 ZCKM5 ZCKMD31H7 ZCKM5H29 ZCKSD35H29 ZCKL6 ZCKMD39H7 ZCKMD39 ZCKS1H29 ZCKM1 ZCKLD37H7 ZCKS6 ZCKS6H29 ZCKMD37H29 ZCKM7 ZCKMD35H29 ZCKS5 ZCKM8H29 ZCKM1H7 ZCKS8H29 ZCKL8H7 ZCKSD37H29 ZCKS2 ZCKS5H29 ZCKS1 ZCKM8 ZCKM6H7 ZCKL6H7 ZCKS9H29 ZCKSD39 ZCKM9H29 ZCKMD31H29 ZCKL1H7 ZCKS8 ZCKMD35 ZCKMD39H29 ZCKMD37H7 ZCKMD37 ZCKSD31H29 ZCKM6H29 ZCKLD31H7 ZCKLD35H7 ZCKSD39H29 ZCKLD37 ZCKL7 ZCKM6 ZCKM9 ZCKS7 ZCKS2H29 ZCKMD35H7 ZCKL8 ZCKSD31 ZCKM5H7 ZCKM8H7 ZCKL1 ZCKSD37 ZCKM1H29 ZCKLD35 ZCKL7H7 ZCKSD35
Movement of operating head	Multi-directional
Type of operator	Cat's whisker spring return metal
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Metal

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	00785901646778
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Package 1 Height	0.330 dm
Package 1 width	0.650 dm
Package 1 Length	2.200 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------