

DCLN steel boring bar, negative right

For facing and longitudinal turning with CN indexable insert

WIDIA 

Application:

For facing and longitudinal turning with CN indexable insert, 80°

Execution:

- Precision-manufactured steel boring bar, internal cooling, type C, pitch angle 95°, tip angle 80°, clearance angle 0°

Advantage:

- Universal use for facing and longitudinal turning
- Negative body geometry ensures good stability and absorption of force for large cutting depths



Art. no.	17684 003
Brand	WIDIA
Manufacturer Part Number	5696073
ISO name	A 32 S DCLN R/L 12
Min. bore diameter	40 mm
Shank diameter	32 mm
Length	250 mm
Programming size	22 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Right
Gross Weight	1.434 kg
Product Group	1XG

EAN

4050841467452